

VAL-CO® Controls Automate Ventilation.

Ovation Series

Display and Set-up Panel:

- 5 character LED display screen shows longer descriptions
- Indicator lights for output status show ventilation system at a glance
- Defective probe pilot light
- Independent temperature probe inputs individual readouts
- 16 or more parameters accessed by dial protection with lock out mode switch preventing accidental or unauthorized changes

Control Features:

- Displays absolute temperatures for all stages
- Inside and outside High/Low temperatures for room average recordings
- Optional humidity probe with RH compensation
- Compatible with potentiometer feedback air inlet control
- Minimum Vent Timer selects desired time on and off no limitations
- On/Off stages have selectable 2° F offset
- Sequential power-on with 5 second delay between stages
- Full-speed fan start-up for 2 seconds on variable output
- Motor curves for variable speed fans
- Ramping functions 10 different set points adjustments for current day
- Adjustable heater offset & differential
- 2 heating stages possible for controls w/2 or more thermo stages
- Dual zone heat mode allows 2 heaters on a single stage w/individual sensors
- Easy access to internal adjustments snap on latch

Alarm Features:

- Test mode runs through sequence to test settings and equipment
- Alarms for High/Low and critical temperatures plus power failure
- Offset alarm for mist, heat and stage 2
- Includes standard alarm output

Curtain Setup:

- Simplified curtain/winch set-up using targeted temperature (absolute values)
- Curtain/winch can be set up to operate anywhere within ventilation control sequence
- Manual overrides for curtains
- Outdoor temperature influence on high alarm offset and curtain logic
- Normal and progressive timing option for curtains
- Built-in adjustable timer on natural ventilation stages



The VAL-CO Family

Watering Systems

• Feed Bins, Fill Systems

Feeders

Ventilation Fans

Inlets

Heaters

Evaporative Cooling

Whole House ControllersTM

Incinerators

Crates, Stalls, Penning

Flooring

Performance You Can Count On





Ovation 113

5 - Stage Control for Power/Natural Applications 1 Variable Speed Stage 1 Curtain Winch Stage 1 On/Off Ventilation Stage 1 Mister Cycle Stage 1 Heater Stage



Ovation 214

7- Stage Control for
Power/Natural Applications
2 Variable Speed Stages
1 Curtain Winch Stage
2 On/Off Ventilation Stages
1 Mister Cycle Stage
1 Heater Stage



Ovation 224

8 – Stage Control for Power/Natural Applications 2 Variable Speed Stages 2 Curtain Winch Stages 2 On/Off Ventilation Stages 1 Mister Cycle Stage 1 Heater Stage



Specifications

TEMPERATURE RANGE

 Operation:
 From 32° F to 122° F (0° C to 50° C)

 Storage:
 From -4° F to 131° F (-20° C to 55° C)

 Readout:
 From -40° F to 120° F (-40° C to 48.9° C)

 Adjustable set point:
 From -40° F to 120° F (-40° C to 48.9° C)

POWER SUPPLY

OUTPUTS

No. of outputs:	22	2 variable and 2 on/off
	24	2 variable and 4 on/off
	113	1 variable and 5 on/off (including curtain relays)
	214	2 variable and 6 on/off (including curtain relays)
	224	2 variable and 8 on/off (including curtain relays)

Fan motor curves:

Choice of 10 motor curves for variable speed fans

Alarm relay:

30 V, 1 A, NO & NC, 1 A fuse (general purpose)

On/Off relays:

1 HP @ 250 VAC; 0.5 HP @ 125 VAC

10 A @ 125/250 V (RES.)

TEMPERATURE PROBES

 No. of temperature probes:
 1 Standard, 3 optional

 Model:
 ZC1353

 No. of wires:
 2

 Temperature range:
 -40° F to 168.8° F (-40° C to 76° C)

 Extension:
 Can be extended up to 700 ft. (213.36 m)

 HOUSING
 Height
 x
 Width
 x
 Depth

 Dimensions:
 10 in. (25.40 cm)
 x
 12 in. (30.48 cm)
 x
 6 in. (15.24 cm)

 Weight:
 6 lbs. (96 gm)

 Material:
 PVC

 Norms:
 NEMA

*Water and dust-tight; protected both indoors and outdoors against splashing water, seepage and falling water or hose-directed water and severe external condensation.

Call your local VAL-CO representative or distributor for more information on these and our other fine products.

North America:

Phone: 800-99VALCO (800-998-2526)

Fax: (+1) 419-678-2200

E-mail: sales@val-co.com

International: Phone: (+1) 419-678-8731 Fax: (+1) 419-678-2200 E-mail: intl.sales@val-co.com

LIT26033 ©2012 VAL-CO 0112XK